


Push-in bulkhead connector QSS-F-14

Part number: 570445

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal size	13 mm
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	3
Food safety	to manufacturer's declaration
Ambient temperature	0 ... 150 °C
Authorization	Germanischer Lloyd
Product weight	112 g
Pneumatic connection, port 1	Push-in sleeve QS-14
Pneumatic connection, port 2	Push-in sleeve QS-14
Materials note	Conforms to RoHS
Materials information, housing	Brass Chromium and nickel plated
Materials information for tubing seal	FPM