

# Plastic tubing PAN-M-12X1,5-NT

Part number: 572090

FESTO



## Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	70 mm
Inside diameter	9 mm
Min. bending radius	50 mm
Temperature dependent working pressure	-0.95 ... 26 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Ambient temperature	-60 ... 100 °C
Product weight according to length	0.051 kg/m
Color	neutral
Shore hardness	D 65 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	Polyamide 12