

Manifold strip

VABM-L1-14G-G14-6-GR

Part number: 573491

FESTO



Data sheet

Feature	Value
Grid dimension	16 mm
Assembly position	Any
Max. number of valve positions	6
Authorization	c UL us - Recognized (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-20 ... 60 °C
Product weight	1,101 g
Auxiliary pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 5	G1/4
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminum alloy