

# Manifold strip

## VABM-L1-10G-G18-24-M-GR

Part number: 573929

FESTO



### Data sheet

| Feature                                 | Value                         |
|---|-------------------------------|
| Grid dimension                          | 10.5 mm                       |
| Assembly position                       | Any                           |
| Max. number of valve positions          | 24                            |
| Authorization                           | c UL us - Recognized (OL)     |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity                         | VDMA24364-B1/B2-L             |
| Storage temperature                     | -20 ... 60 °C                 |
| Product weight                          | 1,009 g                       |
| Auxiliary pilot air port 12/14          | M5                            |
| Pilot exhaust port 82/84                | M5                            |
| Pneumatic connection, port 1            | G1/8                          |
| Pneumatic connection, port 3            | G1/8                          |
| Pneumatic connection, port 5            | G1/8                          |
| Materials note                          | Conforms to RoHS              |
| Material manifold                       | Wrought Aluminum alloy        |