

Electrical sub-base VAVE-L1-1VK7-LP

Part number: 573942

★ Core product range

FESTO



Data sheet

Feature	Value
Cable attribute	For static applications
Polarity protected	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	24 V 12 V
Surge strength	0.8 kV
Degree of contamination	3
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Protection class	IP65
Ambient temperature	-5 ... 60 °C
Assembly position	Any
Max. tightening torque	0.27 Nm
Min. cable bending radius	34 mm
Product weight	20 g
Electrical connection	2-pin / 2-wire Angled socket / cable Square design/open end
Cable structure	2x0,25
Cable diameter	3.4 mm
Cable diameter tolerance	± 0,1 mm
Cable length	1 m
Wire ends	Wire end ferrule
Protective earth connection	Not available
Mounting type	On solenoid valve with self-tapping screw
Housing color	Black
Materials note	Conforms to RoHS
Material cover	PA
Material seals	EPDM
Material housing	PA
Material cable sheath	TPV
Material screws	Heat-treatment steel