

Linear gantry DHSL-2-DGC25S-DGEA18

Part number: 574507

FESTO

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



Data sheet

Feature	Value
Assembly	Linear gantry 2
Effective load	0 ... 2 kg
Drive unit, Z axis	DGEA-18
Drive system, Z axis	Electrical toothed belt actuator
Intermediate position, Z axis	Any
Stroke, Z axis	0 ... 600 mm
Repetition accuracy in the end position, Z axis	± 0,05 mm
Repetition accuracy in the intermediate position, Z axis	± 0,05 mm
Drive unit, Y axis	DGC-25
Drive system, Y axis	Pneumatic
Intermediate position, Y axis	x1
Stroke, Y axis	0 ... 8,500 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm
Repetition accuracy in the intermediate position, Y axis	± 0,02 mm