


Linear gantry DHSL-6-DGC40S-EGSA60

Part number: 574519

FESTO

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



Data sheet

Feature	Value
Assembly	Linear gantry 6
Effective load	0 ... 6 kg
Drive unit, Z axis	EGSA-60
Drive system, Z axis	Electrical With spindle
Intermediate position, Z axis	Any
Stroke, Z axis	0 ... 200 mm
Repetition accuracy in the end position, Z axis	± 0,01 mm
Repetition accuracy in the intermediate position, Z axis	± 0,01 mm
Drive unit, Y axis	DGC-40
Drive system, Y axis	Pneumatic
Intermediate position, Y axis	x1
Stroke, Y axis	0 ... 8,500 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm
Repetition accuracy in the intermediate position, Y axis	± 0,02 mm