


# Linear gantry

## DHSL-10-EGC120TB-DGSL25

Part number: 574525

FESTO

Please click above on symbol FAX request, to obtain a non-binding offer to fulfill your requirements.



### Data sheet

Feature	Value
Assembly	Linear gantry 10
Effective load	0 ... 10 kg
Drive unit, Z axis	DGSL-25
Drive system, Z axis	Pneumatic
Stroke, Z axis	0 ... 200 mm
Repetition accuracy in the end position, Z axis	$\pm 0,01$ mm
Drive unit, Y axis	EGC-120-TB
Drive system, Y axis	Electrical Toothed belt actuator with ball bearing guide
Intermediate position, Y axis	Any
Stroke, Y axis	0 ... 8,500 mm
Repetition accuracy in the end position, Y axis	$\pm 0,08$ mm
Repetition accuracy in the intermediate position, Y axis	$\pm 0,08$ mm