


Supply plate

VABF-B10-20-P1A4-G18

Part number: 576492

FESTO



Data sheet

Feature	Value
Operating pressure MPa	-0.09 ... 1 MPa
Working pressure	-0.9 ... 10 bar
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Max. tightening torque	1.4 Nm
Product weight	78 g
Mounting type	with through hole
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 3	G1/8
Pneumatic connection, port 5	G1/8
Materials note	Conforms to RoHS
Material supply plate	Aluminum die cast