


# Guide cylinder

## DFM-32-50-B-PPV-A-KF

Part number: 609359

FESTO

The proximity switch, type SMTSO-8E, can be used with this product with stroke lengths equal to or greater than 50 mm. The corresponding mounting kit, type SMB-8E, is mounted inwardly or outwardly.



### Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 50 mm   |
| Piston diameter  | 32 mm   |
| Operating mode of drive unit                             | Yoke  |
| Cushioning   | PPV: Pneumatic cushioning adjustable at both ends                           |
| Assembly position  | Any   |
| Guide  | Recirculating ball bearing guide  |
| Design structure   | Guide   |
| Position detection                                       | For proximity sensor  |
| Operating pressure MPa                                   | 0.15 ... 1 MPa  |
| Mode of operation  | double-acting   |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 0 - No corrosion stress   |
| PWIS conformity  | VDMA24364-B1/B2-L   |
| Ambient temperature                                      | -5 ... 60 °C  |
| Impact energy in end positions                           | 0.4 J   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 415 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 482 N   |
| alternative connections                                  | See product drawing   |
| Pneumatic connection                                     | G1/8  |
| Material cover   | Wrought Aluminum alloy  |
| Material seals   | NBR   |
| Material housing   | Wrought Aluminum alloy  |
| Material piston rod                                      | High alloy steel, non-corrosive   |