


L quick connector GCK-3/8-PK-9-KU

Part number: 6272

FESTO

Polymeric design.



Data sheet

Feature	Value
Nominal size	8 mm
Assembly position	Any
Design	L-shape
Container size	10
Operating pressure for entire temperature range	-0.095 ... 1 MPa
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating pressure for entire temperature range	-13.775 ... 145 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Pneumatic connection, port 1	Male thread R3/8
Pneumatic connection, port 2	for barbed connector internal diameter 9 mm with nut
Material of union nut	POM
Material of threaded plug	POM
Materials note	Conforms to RoHS