

Push-in/threaded L-fitting QSL-G1/4-8-C25-50

Part number: 8005394

FESTO



Data sheet

| Feature | Value |
|-----------------------------------------------|----------------------------------------------------------|
| Size | Standard |
| Nominal size | 2.5 mm |
| Type of seal on screw-in stud | Sealing ring |
| Assembly position | Any |
| Container size | 50 |
| Design structure | Push/pull principle |
| Operating pressure complete temperature range | -0.95 ... 16 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 |
| Ambient temperature | -20 ... 80 °C |
| Max. tightening torque | 15 Nm |
| Product weight | 1,375 g |
| Pneumatic connection | Male thread G1/4 For tubing outside diameter 8 mm |
| color of release ring | Black |
| Materials note | Conforms to RoHS |
| Materials information, housing | Brass Nickel plated |
| Materials information for thread seal | NBR |
| Materials information for tubing seal | NBR |
| Hose clamping segment material data | High alloy steel, non-corrosive |