


# Subbase VMPA14-IC-AP-S-1

Part number: 8023667

FESTO



## Data sheet

Feature	Value
Width	24.4 mm
Length	107.3 mm
Grid dimension	14.9 mm
Operating pressure MPa	0.3 ... 0.8 MPa
Working pressure	3 ... 8 bar
Pilot pressure MPa	0.3 ... 0.8 MPa
Pilot pressure	3 ... 8 bar
Authorization	c UL us - Recognized (OL)
KC mark	KC-EMV
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 ... 50 °C
Product weight	150 g
Electrical connection	M8 Plug
Mounting method for subbase	with through hole
Auxiliary pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	M7 G1/8
Pneumatic connection, port 2	M7 G1/8
Pneumatic connection, port 3	M7 G1/8
Pneumatic connection, port 4	M7 G1/8
Pneumatic connection, port 5	M7 G1/8
Materials note	Conforms to RoHS
Material of connecting plate	Aluminum die cast