

# Connector block

## VABM-B10-25S-N38-7

Part number: 8026275

FESTO



### Data sheet

Feature	Value
Grid dimension	27.5 mm
Assembly position	Any
Max. number of valve positions	7
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Product weight	1,143 g
Mounting type	with through hole
Pneumatic connection, port 1	3/8 NPT
Pneumatic connection, port 3	3/8 NPT
Pneumatic connection, port 5	3/8 NPT
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminum alloy