

# Connector block

## VABM-B10-25E-G12-7-P3

Part number: 8026284

FESTO



### Data sheet

| Feature                                 | Value                         |
|---|-------------------------------|
| Grid dimension                          | 27.5 mm                       |
| Assembly position                       | Any                           |
| Max. number of valve positions          | 7                             |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity                         | VDMA24364-B1/B2-L             |
| Product weight                          | 1,896 g                       |
| Mounting type                           | with through hole             |
| Pilot air port 12                       | G1/8                          |
| Pneumatic connection, port 1            | G1/2                          |
| Pneumatic connection, port 3            | G1/2                          |
| Materials note                          | Conforms to RoHS              |
| Material manifold                       | Wrought Aluminum alloy        |