


End plate

VABE-S1-2RZ-G34

Part number: 8032672

FESTO



Data sheet

Feature	Value
Width	44 mm
Exhaust-air function	Via throttle plate
Based on the standard	ISO 5599-1
Operating pressure MPa	0 ... 1 MPa
Working pressure	0 ... 10 bar
Suitability for vacuum	Yes
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-20 ... 60 °C
Medium temperature	-10 ... 50 °C
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-10 ... 50 °C
Product weight	370 g
Mounting type	Via through-hole for M6 screw
Auxiliary pilot air port 12/14	G1/4
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 3	G3/4
Pneumatic connection, port 5	G3/4
Materials note	Conforms to RoHS
Material end plate	Aluminum die cast