


Axial kit EAMM-A-L48-40G

Part number: 8063480

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	12.5 Nm
Product weight	527 g
Interface code, actuator	L48
Interface code, motor in	40G
Materials note	Conforms to RoHS