

Dummy plug NEAC-M-S-BD-R3SCPP

Part number: 8090740

FESTO



Data sheet

Feature	Value
Width	34 mm
Height	22.4 mm
Length	69.2 mm
Product weight	75.4 g
Pack size	1
Electrical connection 1, connection technology	for RJ45 and SC-RJ
Electrical connection 1, type of mounting	Push-Pull
Degree of protection	IP65 IP67
Note on degree of protection	In mounted state
Ambient temperature	-40 °C...70 °C
Storage temperature	-40 °C...70 °C
LABS (PWIS) conformity	VDMA24364-A1-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
Housing colour	Silver
Housing material	Die-cast zinc, nickel-plated
Seals material	NBR
Fire tested	UL94 V-0