

Electronics module VMPA-MPM-EMM-P5

Part number: 8111881

FESTO



Data sheet

Feature	Value
Max. number of valve positions	1
Max. number of solenoid coils	1
Polarity protected	Yes
DC operating voltage, load voltage	21.6 ... 26.4 V
Nominal breakaway current per solenoid coil	60 mA up to 30 ms
Nominal current with current reduction	22 mA after 30 ms
Electrical isolation channel – internal bus	No
Corrosion resistance classification CRC	1 - Low corrosion stress (when installed)
PWIS conformity	VDMA24364 zone III
Ambient temperature	-5 ... 50 °C
Product weight	20 g
Electrical connection	Multi-pin plug
Material housing	POM
Materials note	Conforms to RoHS