

Blanking plug NPQE-P-S3-P10

Part number: 8113203

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Standard |
| Assembly position | Any |
| Design | Blanking plug |
| Container size | 10 |
| Operating pressure for entire temperature range | -0.095 ... 0.8 MPa |
| Operating pressure complete temperature range | -0.95 ... 8 bar |
| Operating pressure for entire temperature range | -13.775 ... 116 psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Cleanroom class | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Ambient temperature | -5 ... 60 °C |
| Product weight | 0.25 g |
| Pneumatic connection, port 1 | Push-in sleeve diameter 3 mm |
| color of release ring | blue |
| Materials note | Conforms to RoHS |
| Material housing | PBT |
| Material release ring | POM |