


# Proximity Sensor SDBF-FCR-16UL-ZU-K-9-N-LE

Part number: 8117061  
New

FESTO



## Data sheet

Feature	Value
Design	Block design
Materials note	Contains PWIS substances Conforms to RoHS
Measured variable	Position
Measuring principle	Magneto-resistive
Ambient temperature	-4 ... 176 °F
Switch output	Contact-type
Switching element function	Normally open contact
Switch-on time	4 µs
Max. output current	500 mA
Max. contact rating DC	10 W
Voltage drop	3.5 V
Short circuit strength	Yes
Operating voltage range AC	5 ... 120 V
Operating voltage range DC	5 ... 120 V
Polarity protected	Yes
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	2
Connector exit direction	axial
Cable sheath color	Grey
Material cable sheath	PVC
Mounting type	With mounting kit
Assembly position	Any
Housing color	transparent
Material housing	PA
Operating status display	LED
Ambient temperature with flexible cable installation	-4 ... 176 °F
Protection class	IP67 NEMA 4