


Handling module EHMZ-EGSC-45-BS-KF-

Part number: 8122331

FESTO



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Working stroke	50 ... 125 mm
Spindle diameter	8 mm
Spindle pitch	8 mm/U
Assembly position	Vertical
Design structure	Electromechanical linear module With spindle
Position detection	For proximity sensor
Max. acceleration	15 m/s ²
Max. speed	0.6 m/s
Repetition accuracy	±0,015 mm
Duty cycle	100 %
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 90 %
Protection class	IP40
Ambient temperature	5 ... 45 °C
Max. feed force F _x	120 N
Feed constant	12 mm/U
Materials note	Conforms to RoHS