


Coupling EAMC-67-80-32-32-U

Part number: 8134829

FESTO



Data sheet

Feature	Value
Holder diameter 1	32 mm
Holder diameter 2	32 mm
Size	67
Nominal length	80 mm
Assembly position	Any
Max. speed	4,500 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	326 kgmm ²
Transferable torque	180 Nm
Product weight	490 g
Materials note	Conforms to RoHS