

# Power supply unit CACN-3A-1-10-G2

Part number: 8149581

FESTO



## Data sheet

Feature	Value
Width	42 mm
Height	130 mm
Length	160 mm
Assembly position	Free convection
Primary supply	Single-phase
Input current	1,3 - 3,1 A
Nominal output voltage DC	24 V
Nominal output current	10 A
Input voltage range AC	100 ... 240 V
Power failure buffering	20 ms
Line frequency	45 ... 65 Hz
Authorization	c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
PWIS conformity	VDMA24364 zone III
Storage temperature	-40 ... 85 °C
Relative air humidity	95 %
Protection class	IP20
Ambient temperature	-25 ... 70 °C
Product weight	1,168 g
Mounting type	with top-hat rail
Materials note	Conforms to RoHS