

Connector kit DADG-AK-G8-10-100

Part number: 8152372

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 10 |
| Stroke | 100 mm |
| Operating pressure MPa | 0.1 ... 0.8 MPa |
| Working pressure | 1 ... 8 bar |
| Operating pressure | 14.5 ... 116 psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 ... 60 °C |
| Max. tightening torque | 1.5 Nm |
| Tightening torque tolerance | ± 10 % |
| Max. tightening torque, pneumatic connection 1 | 0.7 Nm |
| Product weight | 15.5 g |
| Pneumatic connection | M5 |
| Material adapter | Epoxy resin |
| Material seals | NBR |
| Material screws | Coated steel |