

Sealing ring OL-M7

Part number: 8153155

FESTO



Data sheet

| Feature | Value |
|---|-------------------------------|
| Based on the standard | ISO 16030 |
| Operating pressure for entire temperature range | -0.095 ... 3 MPa |
| Operating pressure complete temperature range | -0.95 ... 30 bar |
| Operating pressure for entire temperature range | -13.775 ... 435 psi |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -40 ... 100 °C |
| Manual tightening at ambient temperature | Yes |
| Nominal tightening torque | 3 Nm |
| Tolerance for nominal tightening torque | ± 20 % |
| Product weight | 0.1 g |
| Pneumatic connection | M7 |
| Materials note | Conforms to RoHS |
| Material stops | Aluminum |
| Material seals | HNBR |