

Plastic tubing

PUN-H-F-8X1,25-RT

Part number: 8153393

FESTO

This product is suitable for use with the fittings series types: QS, NPQP, NPQM, CRQS and CK.



Data sheet

Feature	Value
Outside diameter	8 mm
Bending radius relevant for flow rate	37 mm
Inside diameter	5.7 mm
Min. bending radius	21 mm
Instructions for use	Tubing without printing TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
Operating pressure complete temperature range	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 1 MPa
Temperature dependent working pressure	-0.95 ... 10 bar
Temperature-dependent operating pressure	-13.775 ... 145 psi
Note on working pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See declaration of conformity
Ambient temperature	-35 ... 60 °C
Product weight according to length	0.0285 kg/m
Pneumatic connection	For push-in connector outside diameter 8 mm for barbed connector internal diameter 6 mm with nut
Color	Red
Shore hardness	D 52 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)