

# Connector kit DADG-AK-G8-20-150

Part number: 8159797

FESTO



## Data sheet

| Feature  | Value  |
|--|--|
| Size   | 20   |
| Stroke   | 150 mm   |
| Operating pressure MPa                         | 0.1 ... 0.8 MPa  |
| Working pressure                               | 1 ... 8 bar  |
| Operating pressure                             | 14.5 ... 116 psi   |
| Operating medium                               | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Corrosion resistance classification CRC        | 1 - Low corrosion stress                                 |
| PWIS conformity                                | VDMA24364-B1/B2-L  |
| Ambient temperature                            | -10 ... 60 °C  |
| Max. tightening torque                         | 3 Nm   |
| Tightening torque tolerance                    | ± 10 %   |
| Max. tightening torque, pneumatic connection 1 | 3 Nm   |
| Product weight                                 | 58.6 g   |
| Pneumatic connection                           | G1/8   |
| Material adapter                               | Epoxy resin  |
| Material seals                                 | FPM  |
| Material screws                                | Coated steel   |