

# Plastic tubing PUN-H-SF-16X3,1-BL

Part number: 8167911

FESTO



## Data sheet

Feature	Value
Outside diameter	16 mm
Bending radius relevant for flow rate	73 mm
Inside diameter	9.85 mm
Min. bending radius	30 mm
Instructions for use	TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 ... 0.6 MPa
Operating pressure complete temperature range	-0.95 ... 6 bar
Operating pressure for entire temperature range	-13.775 ... 87 psi
Temperature-dependent operating pressure	-0.095 ... 1.3 MPa
Temperature dependent working pressure	-0.95 ... 13 bar
Temperature-dependent operating pressure	-13.775 ... 188.5 psi
Note on working pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.7 MPa at 0 - 60°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water (liquid, free of ice)
Material fire test	UL94 HB
PWIS conformity	VDMA24364-B2-L
Cleanroom class	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Food-safe	See Supplementary material information
Ambient temperature	-35 ... 80 °C
Product weight according to length	0.145 kg/m
Pneumatic connection	For push-in connector outside diameter 16 mm
Color	blue
Shore hardness	D 54 +/-3
Materials note	Conforms to RoHS
Material tubing	TPE-U(PU)