


Pressure gauge

PAGN-40-0.6M-R18-1.6-CPA

Part number: 8178624
New

FESTO



Data sheet

| Feature | Value |
|------------------------------------|-------------------------------|
| Display range | 0 ... 0.6 MPa |
| Conforms to standard | EN 837-1 |
| Nominal size of pressure gauge | 40 |
| Design structure | Bourdon-tube pressure gauge |
| Mounting type | Line installation |
| Operating medium | Inert gases Neutral fluids |
| Operating pressure MPa | 0 ... 0.6 MPa |
| Working pressure | 0 ... 6 bar |
| Operating pressure | 0 ... 87 psi |
| Alternating load factor | 0.66 |
| Measurement accuracy class | 1,6 |
| Protection class | IP43 |
| Storage temperature | -40 ... 70 °C |
| Medium temperature | -20 ... 60 °C |
| Ambient temperature | -20 ... 60 °C |
| PWIS conformity | VDMA24364-B1/B2-L |
| Materials note | Conforms to RoHS |
| Position of connection | Rear side central |
| Pneumatic connection | R1/8 |
| Materials in contact with media | Brass |
| Material of threaded plug | Brass |
| Material housing | ABS |
| Material screen | PS |
| Housing color | Black |
| Product weight | 60 g |
| Note on operating and pilot medium | No acetylene No oxygen |
| Scale | Single scale |