


Flanged pressure gauge PAGN-P-63-0.6M-G14-1-CPA

Part number: 8178634
New

FESTO



Data sheet

Feature	Value
Display range	0 ... 0.6 MPa
Conforms to standard	EN 837-3
Nominal size of pressure gauge	63
Design structure	Bourdon-tube pressure gauge
Mounting type	Front panel installation
Operating medium	Inert gases Neutral fluids
Operating pressure MPa	0 ... 0.6 MPa
Working pressure	0 ... 6 bar
Operating pressure	0 ... 87 psi
Alternating load factor	0.66
Measurement accuracy class	1
Protection class	IP43
Storage temperature	-40 ... 70 °C
Medium temperature	-20 ... 60 °C
Ambient temperature	-20 ... 60 °C
PWIS conformity	VDMA24364-B1/B2-L
Materials note	Conforms to RoHS
Position of connection	Rear side central
Pneumatic connection	G1/4
Materials in contact with media	Brass
Material of threaded plug	Brass
Material housing	ABS
Material screen	SAN
Material mounting ring	Steel
Material screws	Steel
Housing color	Black
Product weight	120 g
Note on operating and pilot medium	No acetylene No oxygen
Scale	Single scale