

Mounting flange adapter DARQ-K-X1-A3-F05-R15

Part number: 8183117

FESTO



Data sheet

Feature	Value
Mounting position	Any
Conforms to standard	ISO 5211 VDI/VDE 3845 (NAMUR)
Structural design	Mounting adapter
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 1 VDI/VDE 3845 size AA 2 VDI/VDE 3845 size AA 3
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...50 °C
Ambient temperature	-20 °C...70 °C
Product weight	100 g
Type of mounting	On flange as per ISO 5211
Note on materials	RoHS-compliant
Material of mounting bracket	PA66, electrically conductive
Mounting adapter material	PA66, electrically conductive
Nut material	High-alloy stainless steel
Disc material	High-alloy stainless steel
Material of screws	Stainless steel