

Gripper finger cap HAMA-GA-B33-40-2-S-40-BU

Part number: 8203480

FESTO



Data sheet

Feature	Value
Size	40
Min. diameter to be gripped	30 mm
Max. diameter to be gripped	55 mm
Working stroke	0 mm...55 mm
Number of Gripper fingers	2
Design	for pneumatic gripper
Structural design	form-fit frictionally engaged
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
For use in the food industry	See supplementary material information
Ambient temperature	0 °C...60 °C
Product weight	68 g
Color	Blue
Shore hardness	A 40 +5
Note on materials	RoHS-compliant
Gripper finger material	VMQ (silicone), metal detectable