

# Gripper finger cap HAMA-GA-B33-100-4-S-40-BU

Part number: 8203482

FESTO



## Data sheet

Feature	Value
Size	100
Min. diameter to be gripped	80 mm
Max. diameter to be gripped	110 mm
Working stroke	30 mm...125 mm
Number of Gripper fingers	4
Design	for pneumatic gripper
Structural design	form-fit frictionally engaged
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
For use in the food industry	See supplementary material information
Ambient temperature	0 °C...60 °C
Product weight	315 g
Color	Blue
Shore hardness	A 40 +5
Note on materials	RoHS-compliant
Gripper finger material	VMQ (silicone), metal detectable