

Gripper finger cap
HAMA-GA-B33-70-3-S-40-BU
Part number: 8203485

FESTO



Data sheet

Feature	Value
Size	70
Min. diameter to be gripped	55 mm
Max. diameter to be gripped	80 mm
Working stroke	20 mm...90 mm
Number of Gripper fingers	3
Design	for pneumatic gripper
Structural design	form-fit frictionally engaged
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364 zone III
For use in the food industry	See supplementary material information
Ambient temperature	0 °C...60 °C
Product weight	114 g
Color	Blue
Shore hardness	A 40 +5
Note on materials	RoHS-compliant
Gripper finger material	VMQ (silicone), metal detectable