

Gripper finger HAFH-B30-16-45-N

Part number: 8207226

FESTO



Data sheet

Feature	Value
Size	16
Mounting position	Any
Design	for pneumatic gripper
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-5 °C...50 °C
Product weight	42 g
Type of mounting	Screwed on to pneumatic gripper
Note on materials	RoHS-compliant
Gripper jaw material	Anodized wrought aluminum alloy
Cap material	POM
Plate material	Wrought aluminum alloy, anodized
Material of screws	Steel, galvanized
Centering pin material	Steel
Gripper finger material	Wrought aluminum alloy, anodized