

Solenoid coil VACF-B-B1-1

Part number: 8220305

FESTO



Data sheet

Feature	Value
Mounting position	Any
Conforms to standard	IEC 61010-1
Duty cycle	100%
Insulation class	H
Coil characteristics	24 V DC: 3.3 W
Permissible voltage fluctuations	+/- 10 %
Certification	c UL us - Recognized (OL)
Certificate issuing authority	UL MH18122
Restricted ambient and media temperature	-20 - 50 °C for block mounting
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-20 °C...60 °C
Degree of protection	IP65
Ambient temperature	-20 °C...60 °C
Product weight	49 g
Electrical connection	Form B as per EN 175301-803
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	PA Steel
Solenoid coil material	Copper Steel Thermoplastic
Material of winding	Copper