

# Cable NEYM-F- -Q9

Part number: 8242219

FESTO



## Data sheet

Feature	Value
Product weight	0.223 kg...6.69 kg
DC operating voltage range	0 V...850 V
Operating voltage range AC	0 V...630 V
Current rating	17.8 A
Protective earth connection	Not available
Cable diameter	11.5 mm
Cable design	4 x 1.5 mm <sup>2</sup> + (2 x 0.75 mm <sup>2</sup> ) + (4 x 0.14 mm <sup>2</sup> + 2 x 0.2 mm <sup>2</sup> )
Degree of protection	IP00
Ambient temperature	90 °C
Ambient temperature with flexible cable installation	90 °C
Storage temperature	70 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material of cable sheath	TPE-E
Color cable sheath	Gray