

Double nipple E-G1/8-1/8NPT

Part number: 9630

FESTO

With 2 sealing rings.



Data sheet

Feature	Value
Nominal size	5.95 mm
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Max. tightening torque, pneumatic connection 1	6 Nm
Max. tightening torque, pneumatic connection 2	7 Nm
Nominal tightening torque	10.55 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	9.1 g
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	1/8 NPT
Materials note	Conforms to RoHS