

Plastična savitljiva cijev PUN-H-2X0,4-SW

Broj artikla: 133039

FESTO

dopušteno u prehrambenom području (postojano na hidrolizu).



Tehnički podaci

Svojstvo	Vrijednost
Vanjski promjer	2 mm
Radijus savijanja, mjerodavan za protok	8 mm
Unutarnji promjer	1,2 mm
Min. radijus savijanja	5 mm
Upute za korištenje	TPE-U Ether basiert
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0,095 ... 0,6 MPa
Pogonski tlak kompletnog temperaturnog područja	-0,95 ... 6 bar
Operating pressure for entire temperature range	-13,775 ... 87 psi
Temperature-dependent operating pressure	-0,095 ... 1 MPa
Pogonski tlak ovisan o temperaturi	-0,95 ... 10 bar
Temperature-dependent operating pressure	-13,775 ... 145 psi
Pogonski medij	Komprimirani zrak prema ISO 8573-1:2010 [7::-:]
PWIS conformity	VDMA24364-B2-L
Klasa čistog prostora	This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly.
Temperatura okoline	-35 ... 60 °C
Težina proizvoda prema duljini	0,0024 kg/m
Pneumatski priključak	For push-in connector outside diameter 2 mm
Boja	crno
Tvrdoća po Shoreu	D 52 +/-3
Materijal - napomena	RoHS sukladno
Material tubing	TPE-U(PU)