

Brtveni prsten OL-1/4

Broj artikla: 34635

FESTO

bez propuštanja, s metalnim tijelom



Tehnički podaci

| Svojstvo | Vrijednost |
|---|--|
| Zasnovano na normi | ISO 16030 |
| Operating pressure for entire temperature range | -0,095 ... 3 MPa |
| Pogonski tlak kompletnog temperaturnog područja | -0,95 ... 30 bar |
| Operating pressure for entire temperature range | -13,775 ... 435 psi |
| Klasa korozione otpornosti KBK | 2 - umjerena otpornost na koroziju |
| PWIS conformity | VDMA24364-B2-L |
| RSBP classification to CD-0033 | F1a |
| Klasa čistog prostora | This product is a static object, active particle generation is not possible when used correctly. Clean product before using it in a cleanroom environment and ensure it is installed correctly. |
| Temperatura okoline | -40 ... 100 °C |
| Ručno pritezanje kod sobne temperature | da |
| Nazivni moment pritezanja | 10 Nm |
| Tolerancija uz nazivni moment pritezanja | ± 20 % |
| Težina proizvoda | 0,32 g |
| Pneumatski priključak | G1/4 |
| Materijal - napomena | RoHS sukladno |
| Material stops | Aluminij |
| Material seals | HNBR |