

Adapter NEFC-M12G5-0.3-U1G5

Broj artikla: 547432

FESTO



Tehnički podaci

Svojstvo	Vrijednost
Vrsta pričvršćenja	na uvrtanje
Električni priključak	5-polno M12x1 Utikači
Duljina kabla	0,3 m
Struktura kabla	4x0,34
Mehanička zaštita	IP20
Temperatura okoline	-5 ... 50 °C
CE znak (vidi izjavu o sukladnosti)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Materijal - napomena	RoHS sukladno
Klasa korozione otpornosti KBK	0 - bez otpornosti na koroziju
Material cable sheath	PUR
Material housing	ABS
Material electrical contact	Brass, gold-plated