


Motorski vod NEBM-S1G9-E- -LE6

Broj artikla: 550743

FESTO

odgovara za koračni motor EMMS-ST...



Tehnički podaci

Svojstvo	Vrijednost
Svojstvo vodiča	prikladno za energetski lanac
Područje pogonskog napona DC	0 ... 72 V
Mehanička zaštita	IP65
Note on degree of protection	u montiranom stanju
Temperatura okoline kod pokretljivog polaganja kablova	-40 ... 70 °C
Temperatura okoline	-40 ... 70 °C
Bending radius, flexible cable installation	≥ 58 mm
Electrical connection 1, function	Field device side
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, design	uglast
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	6
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabel
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	7
Electrical connection 2, occupied pins/wires	6
Krajevi žila	Tuljak završetka žile
Struktura kabla	7x0,34 zaslonjeno
Promjer kabla	8 mm
Duljina kabla	1 ... 25 m
Nazivni presjek vodiča	0,34 mm ²
Cable identification	Without inscription label holder
Boja, kabelski plašt	sivo
Materijal - napomena	RoHS sukladno
Informacija o materijalu, plašt kabla	TPE-U(PUR)