

# Otpor kočenja CACR-LE2-6-W60-V

Broj artikla: 8189339  
Novo

FESTO



## Tehnički podaci

Svojstvo	Vrijednost
Položaj ugradnje	slobodna konvekcija okomito
Pulse energy, braking resistor at 380 V	2.000 Ws
Pulse energy, braking resistor at 780 V	2.000 Ws
Snaga kod 35% ED i 20°C	180 W
Nazivna snaga, otpor kočenja	60 W
Rated output, braking resistor at 380 V	60 W
Rated output, braking resistor at 780 V	60 W
Veličina otpora	6 Ohm
Dozvola	c UL us - Recognized (OL)
PWIS conformity	VDMA24364 zone III
Max. surface temperature	250 °C
Note on surface temperature	Indication at nominal power, at 50% nominal power: 165 °C
Mehanička zaštita	IP54
Temperatura okoline	-40 ... 40 °C
Težina proizvoda	150 g
Vrsta pričvršćenja	s prolaznim provrtom
Materijal - napomena	RoHS sukladno