

# Kampinis kištuko lizdas PEV-1/4-WD-LED-230

Gaminio numeris: 164275

FESTO

slėgio jungikliams, su LED.



## Tech. Duomenys

Savybės	Reikšmė
Atitinka standartus	EN 175301-803
Darbo režimo dispėjus	LED geltonas LED žalias
Montavimo tipas	suspaustas
Cable outlet	Angled
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, connection technology	Plug pattern type A based on EN 175301-803
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Central screw M3
Electrical connection 2, function	Controller side
Electrical connection 2, connection technology	Įsuktas terminalas
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
Nominalus DC įtampos lygis	140 ... 180 V
Nominalus AC įtampos lygis	150 ... 230 V
Leistina srovės apkrova prie 40°C	8 A
Kabelio prijungimas	Pg11
Leistinas kabelio skersmuo	4,5 ... 11 mm
Gnybto skerspjūvis	0,25 ... 1,5 mm <sup>2</sup>
Apsaugos klasė	IP65
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-40 ... 80 °C
Note on ambient temperature	Note derating
CE ženklas (žr. deklaraciją)	atitinka EU reikalavimus žemose įtampose in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Material housing	PA6 sustiprintas
Korpuso spalva	permatomas
Material electrical contact	Žalvaris Nikeliuota Galvanizuota