


Variklio kabelis NEBM-M23G15-EH-10-Q7N-R3LEG14

Gaminio numeris: 5251377

★ Kernprogramm

FESTO



Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	EN 61984
Cable identification	Without inscription label holder
Produkto svoris	3.500 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Hybrid socket
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M23x1
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	12
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Plugs and cables
Electrical connection 2, cable outlet	Tiesus
Electrical connection 2, connection technology	RJ45 and open end
Electrical connection 2, number of pins/wires	14
Electrical connection 2, occupied pins/wires	12
Nominalus DC įtampos lygis	0 ... 850 V
Nominalus AC įtampos lygis	0 ... 630 V
Leistina srovės apkrova prie 40°C	11,7 A
Atsparumas smūgiams	6 kV
Kabelio ilgis	10 m
Kabelio priedas	Suitable for energy chains
Laido bandymo sąlygos	Bandymas pagal užklausimą
Bending radius, fixed cable installation	≥ 48 mm
Bending radius, flexible cable installation	≥ 90 mm
Kabelio skersmuo	12 mm
Kabelio skersmens tolerancija	± 0,3 mm
Kabelio struktūra	4 x 0.75 mm ² + 1 x (2 x 0.75 mm ²) + 1 x (2 x 0.24 mm ² + 2 x 2 x 0.15 mm ²) Ekranuotas
Nominalus laidininko skerspjūvis	0,15 mm ² 0,24 mm ² 0,75 mm ²
Laido galai	Laido antgalis
Apsaugos klasė	IP67
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-40 ... 90 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-25 ... 80 °C
CE ženklas (žr. deklaraciją)	atitinka EU reikalavimus žemose įtampose in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS Be halogeno
Užterštumo laipsnis	1
Atsparumo korozijai klasė CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	pilkas
Material insulation	PP