


# Kabelis

## KV-M12-M12-3,5

Gaminio numeris: 530901

FESTO

Moduliniam elektriniam terminalui CPX.



## Tech. Duomenys

Savybės	Reikšmė
Papildomos funkcijos	Pin 5 of plug leading
Cable identification	su priedais
Prijungimo dažnis	500
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	5
Electrical connection 1, occupied pins/wires	5
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	apvalus
Electrical connection 2, connection type	Kištukas
Electrical connection 2, cable outlet	Tiesus
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	5
Electrical connection 2, occupied pins/wires	5
Electrical connection 2, type of mounting	Screw lock
Nominalus DC įtampos lygis	0 ... 30 V
Nominalus AC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	4 A
Atsparumas smūgiams	1,5 kV
Shielding	Taip
Kabelio ilgis	3,5 m
Kabelio priedas	Standartas
Laido bandymo sąlygos	Bandymas pagal užklausimą
Kabelio skersmuo	5 mm
Kabelio struktūra	4x0,34 Ekranuotas
Nominalus laidininko skerspjūvis	0,34 mm <sup>2</sup>
Apsaugos klasė	IP65 IP67
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-25 ... 70 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 70 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	pilka šviesa

Savybės	Reikšmė
Material housing	TPE-U(PUR)
Korpuso spalva	Juodas
Material screw-type lock	Nickel-plated brass
Material seals	FPM
Material electrical contact	Gold-plated bronze Brass, gold-plated
Material insulation	PVC