


Variklio kabelis NEBM-M16G8-E-15-Q9-LE8-1

Gaminio numeris: 5391550
Nebetiekiamas produktas

FESTO



Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	EN 61984
Cable identification	Without inscription label holder
Produkto svoris	3.500 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M16x0,75
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	6
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	8
Electrical connection 2, occupied pins/wires	6
Nominalus DC įtampos lygis	0 ... 600 V
Note on operating voltage range DC	0 - 300 V for 0.5 mm ²
Nominalus AC įtampos lygis	0 ... 600 V
Note on operating voltage range AC	0 - 300 V for 0.5 mm ²
Leistina srovės apkrova prie 40°C	16 A
Note on acceptable current load at 40°C	8 A for 0.5 mm ²
Atsparumas smūgiams	6 kV
Note on surge resistance	4 kV for 0.5 mm ²
Kabelio ilgis	15 m
Kabelio priedas	Suitable for energy chains
Bending radius, fixed cable installation	≥ 64 mm
Bending radius, flexible cable installation	≥ 128 mm
Kabelio skersmuo	12,8 mm
Kabelio struktūra	4x1,5+2x(2x0,5) Ekranuotas
Nominalus laidininko skerspjūvis	1,5 mm ² 0,5 mm ²
Laido galai	Cable end sleeve to DIN 46228-A..-10 Cable end sleeve to DIN 46228-E..-10
Apsaugos klasė	IP65
Note on degree of protection	Sumontuotas
Aplinkos temperatūra	-50 ... 90 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-40 ... 90 °C
CE ženklas (žr. deklaraciją)	atitinka EU reikalavimus žemose įtampose in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	oranžinis
Material insulation	TPE-E