



# Pajungimo kabelis

## NEBV-C-S7WA44HS-K-10-N-LE36-S10

Gaminio numeris: 577378

FESTO



## Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	DIN 47100
Cable identification	Without inscription label holder
Prijungimo dažnis	50
Produkto svoris	1.800 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	kampinis
Electrical connection 1, connection type	Kištuko lizdas
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	44
Electrical connection 1, occupied pins/wires	36
Electrical connection 1, type of mounting	2 screws 4-40 UNC With seal
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabelis
Electrical connection 2, connection technology	atviri laidai
Electrical connection 2, number of pins/wires	36
Nominalus DC įtampos lygis	0 ... 30 V
Leistina srovės apkrova prie 40°C	0,86 A
Apsaugotas įžeminimas	Negalimas
Kabelio ilgis	10 m
Kabelio priedas	Standartas
Bending radius, fixed cable installation	≥ 39 mm
Bending radius, flexible cable installation	≥ 115 mm
Kabelio skersmuo	9,6 mm
Kabelio skersmens tolerancija	± 0,2 mm
Kabelio struktūra	36x0,25
Nominalus laidininko skerspjuvis	0,25 mm <sup>2</sup>
Apsaugos klasė	IP65 IP67 IP69K
Note on degree of protection	Sumontuotas
Special characteristics	Easy to clean
Aplinkos temperatūra	-5 ... 60 °C
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-5 ... 60 °C
Saugojimo temperatūra	-20 ... 40 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	3 - High corrosion stress
Material cable sheath	PVC
Kabelio apvalkalo spalva	pilkas
Material housing	PA - sustiprintas
Korpuso spalva	pilkas
Material screws	Nerūdijantis plienas
Material seals	EPDM
Material electrical contact	Gold-plated bronze
Material insulation	PVC