



# Paskirstytojas

## NEDY-L2R1-V1-B2W3L-U-0.3L-M8G4-2.5R

Gaminio numeris: 8035781

FESTO



## Tech. Duomenys

Savybės	Reikšmė
Paremtas standartu	EN 61076-2-104
Konstrukcija	Y-distributor with cables on both sides
Distributor type	2 to 1
Signal status display	LED geltonas
Cable identification	With inscription label holder
Montavimo tipas	With through-hole for M2 screw su priedais
Produkto svoris	116 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	apvalus
Electrical connection 1, connection type	Kištukas
Electrical connection 1, cable outlet	Tiesus
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 2, function	Field device side
Electrical connection 2, design	kampinis
Electrical connection 2, connection type	2x rozetė
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connection technology	Plug pattern type B to industry standard, 11 mm
Electrical connection 2, number of pins/wires	3
Electrical connection 2, occupied pins/wires	2
Nominalus DC įtampos lygis	20,4 ... 27,6 V
Leistina srovės apkrova prie 40°C	3 A
Atsparumas smūgiams	0,8 kV
Cable length 1	2,5 m
Cable length 2	0,3 m
Kabelio priedas	Suitable for energy chains/robot applications
Laido bandymo sąlygos	Atsparumas lenkimui pagal Festo normas, bandymo sąlygos pagal užklausimą. Bandymas pagal užklausimą Atsparumas sukimui: > 300 000 Zyklen, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm
Minimum bending radius with freely moveable use 1	39 mm
Minimum bending radius with freely moveable use 2	39 mm
Cable diameter 1	3,8 mm
Cable diameter 2	3,8 mm
Nominalus laidininko skerspjūvis	0,25 mm <sup>2</sup>
Apsaugos klasė	IP65 IP67
Aplinkos temperatūra	-20 ... 80 °C
Note on ambient temperature	-10 ... 40 °C when mounted via through-hole
Aplinkos temperatūra esant lankščiai kabelių instaliacijai	-20 ... 80 °C
Saugojimo temperatūra	-20 ... 80 °C
CE ženklas (žr. deklaraciją)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions

Savybės	Reikšmė
PWIS conformity	VDMA24364-B2-L
Informacija	atitinka RoHS Be halogeno Free of phosphoric acid ester
Užterštumo laipsnis	3
Atsparumo korozijai klasė CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Kabelio apvalkalo spalva	pilkas
Material housing	PA PC TPE-U(PUR)
Korpuso spalva	Juodas
Material of union nut	Nikeliuotas varis
Material seals	NBR
Material electrical contact	Gold-plated copper alloy Silver-plated copper alloy
Material threaded sleeve	Nikeliuotas varis